

Specification Sheet

Part Number: 156-01099

Tie/mount combination eliminates the need to carry multiple sizes of fixed bundle diameter clamps.

Can be assembled directly on harnesses or on production line for installation versatility.

Available in PA66 heat-stabilized or PA46, they are suitable for various temperature grades.

Designed to meet strict automotive standards, they are well adapted to vibration and lateral forces.

Metal inserts withstand high-torque tightening.



H-design allows full contact with harnesses or other tubes and hoses.

Mainly adapted to T120R and T120S cable ties but can also be assembled with smallest sizes.

Dual Cable Ties with Screw Mount, 15" Long, M8 Hole, 120lb, PA46, Grey, 200/box

Article Number 156-01099

Type T120RDHDM8

Color Gray (GY)

Quantity Per pack

Product Description	These cable tie mounts attach with a screw or bolt to an existing hole, or secure to a stud with a nut. They provide an attachment point for securing and routing a single bundle and deliver the highest level of fastening strength for critical cable security.
Short Description	Dual Cable Ties with Screw Mount, 15" Long, M8 Hole, 120lb, PA46, Grey, 200/box
Global Part Name	T120RDHDM8-PA46-GY
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.0
Length L (Metric)	385.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.39

Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	4.13
Bundle Diameter Max (Metric)	105.0
Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	0.61
Height H (Metric)	15.5
Mounting Hole Diameter D (Imperial)	0.33 "
Mounting Hole Diameter D (Metric)	8.4 mm
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)