

Specification Sheet

Part Number: 156-01341



Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

2-piece design allows installer to slide clip around cable tie to obtain optimum orientation

Clip is reusable, making relocation or adjustments simple.

2-Piece Cable Tie with Pipe Clip, 6.0" Long, Attaches to Diameter 0.75 - 0.96", PA66HS/PA66HIRHS, Black, 500/pkg

Article Number 156-01341

Type T50SVCOC19-24.5

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's 2-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.

Short Description 2-Piece Cable Tie with Pipe Clip, 6.0" Long, Attaches to Diameter 0.75 - 0.96", PA66HS/PA66HIRHS, Black, 500/pkg

Global Part Name T50SVCOC19-24.5-PA66HS/PA66HIRHS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.1
Length L (Metric)	155.0
Fixation Method	Omega Clip
Identification Plate Position	none
Tie Closure	plastic pawl
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.35

Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Foot Part Material	PA66HIRHS
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.