

Specification Sheet

Part Number: 156-01555



Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.

Fir tree provides low insertion effort yet demonstrates high extraction resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

2-Piece Cable Tie with Fir Tree Mount, 5.9\"L, 0.22 - 0.25\" Mounting Hole, 100lb, PAEK, Beige, 500/bg

Article Number	156-01555
Type	PAT100RFT6LG
Color	Beige (BGE)
Quantity Per	pack
Product Description	HellermannTyton’s fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Cable Tie with Fir Tree Mount, 5.9\"L, 0.22 - 0.25\" Mounting Hole, 100lb, PAEK, Beige, 500/bg

Global Part Name	PAT100RFT6LG-PAEK-BGE
------------------	-----------------------

Minimum Tensile Strength (Imperial)	100
-------------------------------------	-----

Minimum Tensile Strength (Metric)	445
-----------------------------------	-----

Length L (Imperial)	5.9
---------------------	-----

Length L (Metric)	149.9
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.33
--------------------	------

Width W (Metric)	8.0
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.5
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Height H (Imperial)	0.75
---------------------	------

Height H (Metric)	19.20
-------------------	-------

Panel Thickness Min (Imperial)	0.05
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	1.25
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.22 - 0.25 "
Mounting Hole Diameter D (Metric)	5.6 - 6.4 mm
Mounting Hole Diameter D Min (Imperial)	0.22
Mounting Hole Diameter D Max (Imperial)	0.25
Mounting Hole Diameter D Max (Metric)	6.4
Disc Diameter (Metric)	18.6
Disc Diameter (Imperial)	0.73

Material	Polyaryletherketone (PAEK)
Foot Part Material	PAEK
Material Shortcut	PAEK
Flammability	UL 94 V-0

Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-67°F to +392°F (-55°C to +200°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)