

Specification Sheet


Part Number: 156-01668

Versatile design allows cable routing above, perpendicular or parallel to stud.

Can mount up to three bundles simultaneously, making efficient use of a single mounting point.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.



2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA46, BN/GY, 3000/pkg

Article Number

156-01668

Type

T50R1SBS5-6U-SET

Color

Gray (GY) Brown (BN)

Quantity Per

pack

Product Description

Unique, two-piece design allows routing to be above, parallel or perpendicular to stud. This also enables up to three separate bundles to be fastened to the same stud. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description	2-Piece M5/T5/M6/T6 Stud Mount Tie, 8.0" Tie, 50lb Tensile Strength, PA46, BN/GY, 3000/pkg
Global Part Name	T50R1SBS5-6U-SET-PA46-BN/GY
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	223
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.92
Width W (Metric)	23.25
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0

Cable Ties	156-01668
Height H (Imperial)	0.74
Height H (Metric)	18.75
Mounting Hole Diameter D (Imperial)	0.20 x 0.03 " 0.24 x 0.04 " 0.20 "
Mounting Hole Diameter D (Metric)	T5 M5 x 0.8 M6 x 1
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.0
Stud Diameter (Metric)	6.0 mm 5.0 mm
Stud Diamater (Imperial)	0.20 ", 0.24
Material	Polyamide 4.6 (PA46)
Foot Part Material	PA46
Material Shortcut	PA46
Material Cable Tie	Polyamide 4.6 (PA46)
UV Resistant (Yes/No)	No

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)