

Specification Sheet

Part Number: 156-01812

Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Fixed connector controls routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.



MOC Clip, 6 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-01812
----------------	-----------

Type	T50RMOC6SAD-SET
------	-----------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The MOC with Saddle to T50R Tie has a two-piece design that keeps two routings secured together while providing a fixed orientation for each bundle. The bi-directional saddle design allows the bundles to be coupled parallel or perpendicular to one another. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness.
---------------------	--

Short Description	MOC Clip, 6 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 2000/ctn
-------------------	---

Global Part Name	T50RMOC6SAD-SET-PA66HIRHSUV-BK
------------------	--------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	0.44
---------------------	------

Length L (Metric)	11.1
-------------------	------

Fixation Method	Omega Clip
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Bundle Diameter Min (Imperial)	0.22
--------------------------------	------

Bundle Diameter Min (Metric)	5.5
------------------------------	-----

Bundle Diameter Max (Imperial)	0.27
--------------------------------	------

Bundle Diameter Max (Metric)	6.8
------------------------------	-----

Height H (Imperial)	0.70
---------------------	------

Height H (Metric)	17.9
-------------------	------

Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)