

Specification Sheet

Part Number: 156-02063



Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

MOC Clip to MOC Clip Perpendicular, 10 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Article Number 156-02063

Type MOC10FMOC16M180

Color Black (BK)

Quantity Per pack

Product Description The MOC to MOC 180 is a rotatable dual routing clip that keeps two routings secured and separated. One clip is oriented 90 degrees from the other to provide alternative access for bundle attachment. A swivel coupler allows them to rotate independently of each other.

Short Description MOC Clip to MOC Clip Perpendicular, 10 mm, 16 mm Perpendicular, PA66HIRHSUV, Black, 2000/ctn

Global Part Name MOC10FMOC16M180-PA66HIRHSUV-BK

| | |
|--------------------------------|--|
| Length L (Imperial) | 1.85 |
| Length L (Metric) | 46.92 |
| Variant | Clip to Clip Transverse |
| Bundle Diameter Min (Imperial) | 0.37 |
| Bundle Diameter Min (Metric) | 9.5 |
| Bundle Diameter Max (Imperial) | 0.45 |
| Bundle Diameter Max (Metric) | 11.5 |
| Height H (Imperial) | 0.90 |
| Height H (Metric) | 22.9 |
| Depth D (Imperial) | 0.47 |
| Depth D (Metric) | 12.0 |
| Material | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut | PA66HIRHSUV |
| Flammability | UL 94 HB |

| | |
|------------------------------|-----------------------------------|
| Halogen Free | Yes |
| UV Resistant (Yes/No) | Yes |
| Use Conditions | For Indoor and Outdoor Use |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 1000 |
| Package Quantity (Metric) | 2000 |
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)