

Specification Sheet

Part Number: 156-02225



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap ensuring proper orientation.

2-Piece Cable Tie with Edge Clip, 8.0" Long, EC5B, 1 - 3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 500/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                                                                      |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 156-02225                                                                                                                                                                                                                                                                                                                                                                                            |
| Type                | T50REC5B                                                                                                                                                                                                                                                                                                                                                                                             |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                                                                           |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                                                                 |
| Product Description | HellermannTyton's Two-Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. NOTE: UL Listing applies to 1-2mm panel thicknesses only. |
| Short Description   | 2-Piece Cable Tie with Edge Clip, 8.0" Long, EC5B, 1 - 3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 500/pkg                                                                                                                                                                                                                                                                                      |

|                  |                                       |
|------------------|---------------------------------------|
| Global Part Name | T50REC5B-PA66HIRHSUVR5/PA66HIRHSUV-BK |
|------------------|---------------------------------------|

|                                     |    |
|-------------------------------------|----|
| Minimum Tensile Strength (Imperial) | 50 |
|-------------------------------------|----|

|                                   |     |
|-----------------------------------|-----|
| Minimum Tensile Strength (Metric) | 225 |
|-----------------------------------|-----|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 8.0 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 202.0 |
|-------------------|-------|

|                 |           |
|-----------------|-----------|
| Fixation Method | Edge Clip |
|-----------------|-----------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|         |                 |
|---------|-----------------|
| Variant | Inside Serrated |
|---------|-----------------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.18 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 4.6 |
|------------------|-----|

|                                |     |
|--------------------------------|-----|
| Bundle Diameter Min (Imperial) | 0.2 |
|--------------------------------|-----|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 5.0 |
|------------------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Max (Imperial) | 1.97 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 50.0 |
|------------------------------|------|

|                        |      |
|------------------------|------|
| Thickness T (Imperial) | 0.05 |
|------------------------|------|

|                                |                                                                                                                                                                         |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Thickness T (Metric)           | 1.2                                                                                                                                                                     |
| Height H (Imperial)            | 0.61                                                                                                                                                                    |
| Height H (Metric)              | 1.2                                                                                                                                                                     |
| Panel Thickness Min (Imperial) | 0.04                                                                                                                                                                    |
| Panel Thickness Max (Imperial) | 0.12                                                                                                                                                                    |
| Panel Thickness Min (Metric)   | 1.0                                                                                                                                                                     |
| Panel Thickness Max (Metric)   | 3.0                                                                                                                                                                     |
| Material                       | Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Foot Part Material             | PA66HIRHSUVR5                                                                                                                                                           |
| Material Shortcut              | PA66HIRHSUVR5 PA66HIRHSUV                                                                                                                                               |
| Material Cable Tie             | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)                                                                                                |
| Flammability                   | UL 94 HB                                                                                                                                                                |
| UV Resistant (Yes/No)          | Yes                                                                                                                                                                     |
| Use Conditions                 | For Indoor and Outdoor Use                                                                                                                                              |

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| Operating Temperature        | -40°F to +239°F (-40°C to +115°C) -40°F to +230°F (-40°C to +110°C) |
| Reach Compliant (Article 33) | Yes                                                                 |
| ROHS Compliant               | Yes                                                                 |
| UL Listed (US and Canada)    | Yes                                                                 |
| UL Listed (US)               | Yes                                                                 |
| Package Quantity (Imperial)  | 500                                                                 |
| Package Quantity (Metric)    | 500                                                                 |
| Customs Number               | 3926909988                                                          |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com