

Specification Sheet

Part Number: 156-02227



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Two-piece assembly allows the mount to slide along the strap ensuring proper orientation.

2-Piece Cable Tie with Edge Clip, 8.0" Long, EC5A, 1 - 3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 500/pkg

Article Number	156-02227
Type	T50REC5A
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
Short Description	2-Piece Cable Tie with Edge Clip, 8.0" Long, EC5A, 1 - 3 mm Panel, 50lb, PA66HIRHSUV/PA66HIRHSUVR5, Bk, 500/pkg

Global Part Name	T50REC5A-PA66HIRHSUVR5/PA66HIRHSUV-BK
------------------	---------------------------------------

Minimum Tensile Strength (Imperial)	20
-------------------------------------	----

Minimum Tensile Strength (Metric)	89
-----------------------------------	----

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Edge Clip
-----------------	-----------

Identification Plate Position	none
-------------------------------	------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.2
--------------------------------	-----

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.2
----------------------	-----

Height H (Imperial)	0.61
Height H (Metric)	15.5
Panel Thickness Min (Imperial)	0.04
Panel Thickness Max (Imperial)	0.12
Panel Thickness Min (Metric)	1.0
Panel Thickness Max (Metric)	3.0
Material	Polyamide 6.6, high impact modified, heat and UV-stabilized, proprietary blend (PA66HIRHSUVR5) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUVR5
Material Shortcut	PA66HIRHSUV PA66HIRHSUVR5
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +239°F (-40°C to +115°C) -40°F to +230°F (-40°C to +110°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com