

Specification Sheet

Part Number: 156-02316

Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.



MOC Clip to MOC Clip, 8 mm, 8 mm, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-02316
Type	MOC8FMOC8M
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.
Short Description	MOC Clip to MOC Clip, 8 mm, 8 mm, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	MOC8FMOC8M-PA66HIRHSUV-BK

Length L (Imperial)	1.24
Length L (Metric)	31.5
Variant	Clip to Clip
Bundle Diameter Min (Imperial)	0.28
Bundle Diameter Min (Metric)	7.0
Bundle Diameter Max (Imperial)	0.35
Bundle Diameter Max (Metric)	9.0
Height H (Imperial)	0.60
Height H (Metric)	15.2
Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)