

Specification Sheet

Part Number: 156-02513

Capable of holding several cables, depending on cable tie size, for ultimate flexibility.

Zero-insertion-force design requires no tools for quick and easy mounting.

High impact modified, heat-resistant, UV stabilized material is ideal for long-term performance, even in extreme weather.

Product Image

Article Number

156-02513

Type

T50RPBM9SET

Color

Black (BK)

Quantity Per

pack

Product Description

This button head mount includes a cable tie to secure cables and wire bundles to panels. Once placed through the panel hole, installers can insert the cable tie through the mount on the panel's opposite surface. The button head mount is designed to fit pre-stamped oval hole sizes from 9x12 mm to 9x14 mm with zero insertion force. Made from impact-modified, heat-resistant, UV stabilized Polyamide 6.6 material, it will withstand extreme environments.

Short Description

Cable Tie with Button Mount, 0.35" Hole Dia, 0.12" Max Panel, 0.07" Max Tie Width, PA66HIRHSUV, Black, 1000/pkg

Global Part Name

T50RPBM9SET-PA66HIRHSUV-BK

Contents of pkg/kit

T50R Cable Tie, Button Mount

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Button Head
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.67
Width W (Metric)	17.0
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.53
Height H (Metric)	13.40

Panel Thickness Max (Imperial)	0.12
Panel Thickness Max (Metric)	3.0
Mounting Hole Diameter D (Imperial)	0.35 " 0.35 x 0.47 " 0.35 x 0.55 "
Mounting Hole Diameter D (Metric)	9.0 x 12.0 mm 9.0 x 14.0 mm 9.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35
Mounting Hole Diameter D Max (Imperial)	0.55
Mounting Hole Diameter D Max (Metric)	14.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes

UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)