

Specification Sheet

Part Number: 156-02594

Bundle can rotate to any orientation, allowing routing in any direction regardless of mounting point.

Clip is reusable, making relocation or adjustments simple.

All-in-one bundling and mounting solution reduces costs.



Article Number	156-02594
Type	T50SMVCLOC10-14
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's 1-Piece Cable Tie with Pipe Clip secures cables to tubular frame rails. The cable tie bundles wires, cables or tubes, and the C-clip snaps onto the tubular frame rail. The clip can be removed from the mounting surface and reinstalled without additional fasteners.
Short Description	LOC Locking Clamp, 10 - 14 mm, with T50SMVC Swivel Tie, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	T50SMVCLOC10-14-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.3
Length L (Metric)	210.0
Fixation Method	Omega Clip
Identification Plate Position	none
Width W (Imperial)	0.47
Width W (Metric)	12.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	0.55
Bundle Diameter Max (Metric)	14.0
Height H (Imperial)	0.93
Height H (Metric)	27.4
Depth D (Imperial)	0.47
Depth D (Metric)	12.0

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)