

Specification Sheet

Part Number: 156-02652

One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.



High-performing oval fir trees ensure anti-rotational routing in existing or stamped oval or rectangular holes with no additional hardware required.

Fir Tree Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, FT9X17, PA66HIRHSUV, Black, 200/ctn

Article Number 156-02652

Type IRCDFT9X17

Color Black (BK)

Quantity Per pack

Product Description

The Fir Tree Mount Ratchet Clamp offers versatility when managing wires, cables and hoses. Integrated fir tree means no additional hardware is needed for securing to a hole. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.

Short Description

Fir Tree Mount Ratchet Clamp, 1.42 - 2.0" Bundle Dia, FT9X17, PA66HIRHSUV, Black, 200/ctn

Global Part Name

IRCDFT9X17-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 100

Minimum Tensile Strength (Metric) 445

Length L (Imperial) 1.37

Length L (Metric) 34.8

Fixation Method Fir Tree for oval holes

Width W (Imperial) 1.37

Width W (Metric) 34.9

Bundle Diameter Min (Imperial) 1.42

Bundle Diameter Min (Metric) 36.01

Bundle Diameter Max (Imperial) 2

Bundle Diameter Max (Metric)	50.8
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.35 x 0.67 "
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

UL Listed (US and Canada) Yes

UL Listed (US) Yes

Package Quantity (Imperial) 200

Package Quantity (Metric) 200

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)