

Specification Sheet

Part Number: 156-02987



- Anti-rotation pin eliminates movement of bundle when fastening bolt.
- Heavy duty mount with robust 120 lb tie delivers an ultra strong alternative to metal clamps.
- Assembly withstands vibrations and displacement forces.
- Metal bushing accommodates high tightening torque.

2-Piece Cable Tie with Screw Mount, Unassembled Set, 15" L, M6 Hole, 120lb, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-02987
Type	T120RCPCM6FT6.5SET
Color	Black (BK)
Quantity Per	pack
Product Description	These heavy duty cable tie mounts, secured with mechanical fasteners, include an anti-rotation pin that keeps the mount and harness assembly in position during the torquing of the bolt or nut. They provide an attachment point for securing and routing a single bundle. The mounts provide the highest level of fastening for critical cable security.
Short Description	2-Piece Cable Tie with Screw Mount, Unassembled Set, 15" L, M6 Hole, 120lb, PA66HIRHSUV, Black, 1000/ctn

Global Part Name	T120RCPCM6FT6.5SET-PA66HIRHSUV-BK
------------------	-----------------------------------

Minimum Tensile Strength (Imperial)	120
-------------------------------------	-----

Minimum Tensile Strength (Metric)	535
-----------------------------------	-----

Length L (Imperial)	15.0
---------------------	------

Length L (Metric)	385.0
-------------------	-------

Fixation Method	Screw Mount
-----------------	-------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.30
--------------------	------

Width W (Metric)	7.6
------------------	-----

Bundle Diameter Min (Imperial)	0.2
--------------------------------	-----

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	4.13
--------------------------------	------

Bundle Diameter Max (Metric)	105.0
------------------------------	-------

Thickness T (Imperial)	0.07
Thickness T (Metric)	1.8
Height H (Imperial)	1.11
Height H (Metric)	28.22
Mounting Hole Diameter D (Imperial)	0.24 "
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Max (Metric)	11.3
Stud Diameter (Metric)	6.0 mm
Stud Diamater (Imperial)	0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)