

Specification Sheet

Part Number: 156-03002



Clamp and mount combination means no extra hardware is needed, for time-saving, toolless, one-handed installation.

Three size ranges handle diameters from 0.5" to 2", reducing part inventory.

Clamp saddle provides additional attachment option using a cable tie.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

Quick2Clamp, Ratchet, 0.76" - 1.42" Bundle Dia, 1-5/8" Strut Attachment, PA66HIRHSUV, Black, 200/box

Article Number 156-03002

Type IRCCSTRUT

Color Black (BK)

Quantity Per pack

Product Description The Quick2Clamp offers ultra-fast installation and versatility for managing conduit, tubing and cables. The built-in strut mount attaches with a simple twist. The one-piece design makes it simple to install without tools. Robust, adjustable clamp closes by hand to the desired diameter. A release feature allows easy and nondestructive maintenance simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the strut.

Short Description	Quick2Clamp, Ratchet, 0.76" - 1.42" Bundle Dia, 1-5/8" Strut Attachment, PA66HIRHSUV, Black, 200/box
Global Part Name	IRCCSTRUT-PA66HIRHSUV-BK
Length L (Imperial)	4.56
Length L (Metric)	115.9
Fixation Method	1-5/8 " Strut Attachment
Variant	Load Rating: 17 lbs, Safety Factor: 3 Pull Force Rating: 50 lbs
Width W (Imperial)	1.37
Width W (Metric)	34.81
Bundle Diameter Min (Imperial)	0.76
Bundle Diameter Min (Metric)	19.4
Bundle Diameter Max (Imperial)	1.42
Bundle Diameter Max (Metric)	36.0
Height H (Imperial)	2.04
Height H (Metric)	51.8

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL UL2239 Conduit & Cable Hanger
UL Listed (US)	Yes
Package Quantity (Imperial)	200
Package Quantity (Metric)	200
Customs Number	3926909988