

Specification Sheet

Part Number: 156-03602



Series 7-specific hanger mounts in an instant, significantly reducing install time and repetitive strain injuries.

Impact modified, heat and UV stabilized PA66 provides long-term durability in extreme solar applications.

One-piece ratchet closure design allows for easy installation during pre- or final assembly.

Release feature allows for quick adjustments and maintenance.

Series 7 Ratchet Clamp, 0.76 - 1.42" Bundle Dia, PA66HIRHSUV/ZN/ST, Black, 150/carton

Article Number	156-03602
Type	CMRCCHANGERFS7
Color	Black (BK)
Quantity Per	pack
Product Description	The Series 7 Ratchet Clamp offers one-handed, toolless simplicity and size versatility for managing wires and cables on First Solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. One-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes of single-diameter fasteners. Integrated release feature enables easy and nondestructive removal of cables by inserting a flat-head screwdriver. This allows the clamp to be reused without removing it.

Short Description	Series 7 Ratchet Clamp, 0.76 - 1.42" Bundle Dia, PA66HIRHSUV/ZN/ST, Black, 150/carton
-------------------	--

Global Part Name	CMRCCCHANGERFS7-PA66HIRHSUV/ZN/ST-BK
------------------	--------------------------------------

Minimum Tensile Strength (Imperial)	100
-------------------------------------	-----

Minimum Tensile Strength (Metric)	445
-----------------------------------	-----

Length L (Imperial)	4.93
---------------------	------

Length L (Metric)	125.3
-------------------	-------

Fixation Method	Mounting Hanger
-----------------	-----------------

Width W (Imperial)	1.40
--------------------	------

Width W (Metric)	35.5
------------------	------

Bundle Diameter Min (Imperial)	0.76
--------------------------------	------

Bundle Diameter Min (Metric)	19.3
------------------------------	------

Bundle Diameter Max (Imperial)	1.42
--------------------------------	------

Bundle Diameter Max (Metric)	36.07
------------------------------	-------

Height H (Imperial)	3.39
---------------------	------

Height H (Metric)	86.2
-------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Zinc plated (ZN) Steel (ST)
Material Shortcut	PA66HIRHSUV ST ZN
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)