

Specification Sheet

Part Number: 156-03942



Pre-assembled 2-piece tie with arrowhead mount provides bundling and securing with one assembly.

TPE seal protects against ingress of water and debris.

Cable tie is outside serrated to reduce bundle chafing.

Low profile cable tie helps bundle wires neatly to accommodate wire harnesses with smaller diameters.

Low profile head won't snag on surrounding parts and wires.

2-Piece Low-Profile Cable Tie/Arrowhead w Seal, 1.2 - 1.8mm Panel, 6.5mm/6.35mm HEX, PA66HIRHSUV/TPE, BK, 500/bg

Article Number	156-03942
Type	LPT50RSRAH6.5D1.4TSD
Color	Gray (GY) Black (BK)
Quantity Per	pack

Product Description	HellermannTyton sealed arrowhead mount and tie are constructed of engineered nylon with a dual TPE (thermo plastic elastomer) seal. The combination of dual seal and engineered arrowhead provide superior sealing performance for applications where protection from moisture and debris is essential. Low profile cable tie features a compact, contoured head designed to use less space in confined areas and reduce protrusions that might otherwise interfere with or damage adjacent wire insulation and hoses. The outside serration provides a smooth inside surface to further minimize indentation or damage to soft bundles while offering high tensile strength and low insertion force. This mount is sold as an assembly with the cable tie.
Short Description	2-Piece Low-Profile Cable Tie/Arrowhead w Seal, 1.2 - 1.8mm Panel, 6.5mm/6.35mm HEX, PA66HIRHSUV/TPE, BK, 500/bg
Global Part Name	LPT50RSRAH6.5D1.4TSD-PA66HS/PA66HIRHSUV-BK/GY
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.7
Length L (Metric)	194.6
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18

Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.55
Height H (Metric)	13.85
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Panel Thickness Min (Imperial)	0.05
Panel Thickness Max (Imperial)	0.07
Panel Thickness Min (Metric)	1.2
Panel Thickness Max (Metric)	1.8
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 " (HEXAGONAL) 0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm 6.15 - 6.55 mm (hexagonal)
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27

Mounting Hole Diameter D Max (Metric)	6.9
Material	Polyamide 6.6 heat stabilized (PA66HS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HS PA66HIRHSUV
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)