

Specification Sheet

Part Number: 156-04062



- Pre-assembled self-affixing tie with coupler.
- Cable tie head can be moved after bundling.
- Easy addition of cables after assembly.
- For parallel routing of bundles that can be twisted 90° even after installation.

3-Piece T50R Tie with Coupler, 8" Long, 0.08 - 1.97" Dia, 50lbs, PA66HIRHS/PA66HIRHSUV, Orange/Black, 500/pkg

Article Number	156-04062
Type	T50RCOUPLER
Color	Black (BK) Orange (OG), High Voltage (HV)
Quantity Per	pack
Product Description	The Coupler is the simple way to connect two cable ties for a parallel routing of two bundles. His special design allows the ties 90 degrees of rotation. This is ideal for all applications where the cable, pipe or hose should move flexible in relation to the fixing point. The Coupler can be used with one or two cable ties. This allows easily subsequent installation or replacements of further cables, pipes or hose.
Short Description	3-Piece T50R Tie with Coupler, 8" Long, 0.08 - 1.97" Dia, 50lbs, PA66HIRHS/PA66HIRHSUV, Orange/Black, 500/pkg

Global Part Name	T50RCOUPLER-PA66HIRHS/PA66HIRHSUV-OG/BK
------------------	---

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	7.874
---------------------	-------

Length L (Metric)	202.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.85
--------------------------------	------

Bundle Diameter Max (Metric)	47.0
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	1.97
---	------

Bundle Diameter 1st Loop Max (Metric) 50.0

Bundle Diameter 2nd Loop Max (Imperial) 1.97

Bundle Diameter 2nd Loop Max (Metric) 50.0

Height H (Imperial) 0.33

Height H (Metric) 8.3

Cable Tie Width Max (Imperial) 0.18

Cable Tie Width Max (Metric) 4.70

Disc Diameter (Imperial) 0.47

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Polyamide 6.6 high impact modified, heat and UV stabilized
(PA66HIRHSUV)

Foot Part Material PA66HIRHSUV

Material Shortcut PA66HIRHS PA66HIRHSUV

Flammability UL 94 HB

Halogen Free Yes

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)