

Specification Sheet

Part Number: 156-04065

Pre-assembled 2-piece fixing tie with fir tree foot part.

Cable tie head can be moved after bundling.

Easy to assemble without the need for a tool.

Disc adjusts tie for pressure from various directions and minimises access of dust and dirt.

Fir tree foot part can be used for a variety of panel thicknesses.

Suitable for use within threaded holes.



2-Piece Cable Tie with Fir Tree Mount, 8.0"L, 6.1 - 7.0 mm Mounting Hole, PA66HIRHS/UV, BK/OG, 500/ctn

Article Number	156-04065
Type	T50RX2DUALSDFT6.5A
Color	Black (BK) Orange (OG), High Voltage (HV)
Quantity Per	pack

Product Description	These two-piece self-affixing cable ties are supplied ready assembled and offer a simple and versatile method of bundling and fastening cables. The deep-hole anchor will easily push into blind holes with or without thread and offers a very secure attachment. The two-piece design enables the head of the tie to be oriented to the required position to ease assembly, while the disc on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.
Short Description	2-Piece Cable Tie with Fir Tree Mount, 8.0"L, 6.1 - 7.0 mm Mounting Hole, PA66HIRHS/UV, BK/OG, 500/ctn
Global Part Name	T50RX2DUALSDFT6.5A-PA66HIRHS/PA66HIRHSUV-OG/BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.46
Width W (Metric)	11.7
Bundle Diameter Min (Imperial)	0.06

Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2
Height H (Imperial)	0.80
Height H (Metric)	20.5
Cable Tie Width Max (Imperial)	0.21
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.23
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.28 "
Mounting Hole Diameter D (Metric)	6.1 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.0

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV PA66HIRHS
Material Cable Tie	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)