

Specification Sheet

Part Number: 156-04211



Mount is designed to provide a low push-in force and high pull-out resistance.

Disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Heavy-duty tie design offers higher tensile strength.

Mount design ideal for 6.5 mm or threaded M8 holes.

2-Piece Cable Tie with Fir Tree Mount, Unassembled Set, 9"L, FT6.5/M8 Hole, PA66HIRHSUV, Black, 1000/ctn

Article Number	156-04211
Type	T120SFTM8SET
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton’s fir tree mount provides a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. It is sold as an unassembled set with the cable tie.
Short Description	2-Piece Cable Tie with Fir Tree Mount, Unassembled Set, 9"L, FT6.5/M8 Hole, PA66HIRHSUV, Black, 1000/ctn
Global Part Name	T120SFTM8SET-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	9.0
Length L (Metric)	229.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	2.17
Bundle Diameter Max (Metric)	55.0
Thickness T (Imperial)	0.07

Thickness T (Metric)	1.8
Height H (Imperial)	0.90
Height H (Metric)	22.77
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.26 "
Mounting Hole Diameter D (Metric)	6.0 - 6.9 mm M8 Threaded
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.26
Mounting Hole Diameter D Max (Metric)	6.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV

Material Cable Tie	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com