

Specification Sheet

Part Number: 157-00380



Design gives quick and easy assembly by hand without the need for tools.

Mount can be used in a wide variety of applications where 5mm weld studs or 5mm ISO bolts.

Design provides low insertion force and high extraction force.

Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg

Article Number	157-00380
Type	T50SSBS6OT-E
Color	Black (BK)
Quantity Per	bag
Product Description	The Standoff Stud Mount tie applies easily to weld studs and secures bundles away from fixing holes. These are used primarily in the automotive industry, but can be used in a variety of applications.
Short Description	Standoff Stud Mount Tie, 6.0 mm studs, 6.0" Long, PA66HS, Black, 1000/pkg
Global Part Name	T50SSBS6OT-E-PA66HS-BK

Minimum Tensile Strength (Imperial)	45
Minimum Tensile Strength (Metric)	200
Length L (Imperial)	6.3
Length L (Metric)	160.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Stud Diameter (Metric)	6.0 mm
Stud Diamater (Imperial)	0.24

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)