

Specification Sheet

Part Number: 157-00052



All-in-one bundling and fastening solution reduces costs and assembly time.

Disc feature provides anti-rattle protection in high-vibration applications.

1-Piece Cable Tie with Fir Tree Mount with Disc, 8.5"L, 6.5 - 7.2 mm Mounting Hole, PA66HS, Black, 500/pkg

Article Number

157-00052

Type

T50ROSFT6LGU

Color

Black (BK)

Quantity Per

pack

Product Description

One-piece mounting ties offer a complete solution by both bundling and mounting wires, cables and tubes. The fir tree mount provides low insertion force with a high extraction force. Outside serrations on the cable tie leave a smooth interior surface that's gentler on sensitive wire insulation. The unique head design allows the cable tie to firmly hold bundles as small as .06" diameter. The disc offers added protection against debris.

Short Description

1-Piece Cable Tie with Fir Tree Mount with Disc, 8.5"L, 6.5 - 7.2 mm Mounting Hole, PA66HS, Black, 500/pkg

Global Part Name	T50ROSFT6LGU-PA66HS-BK
------------------	------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	8.6
---------------------	-----

Length L (Metric)	218.44
-------------------	--------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.2
--------------------	-----

Width W (Metric)	5.1
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Imperial)	0.06
Thickness T (Metric)	1.5
Height H (Imperial)	0.06
Height H (Metric)	1.5
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.33
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	8.5
Mounting Hole Diameter D (Imperial)	0.26 - 0.28 "
Mounting Hole Diameter D (Metric)	6.5 - 7.2 mm
Mounting Hole Diameter D Min (Imperial)	0.26
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter (Metric)	16
Disc Diameter (Imperial)	0.63

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com