

Specification Sheet

Part Number: 157-00053

All-in-one bundling and fastening solution reduces costs and assembly time.

Anti-rotational oval fastener forces bundle to travel in intended direction.

High-spec materials and superior design deliver excellent performance and value.



1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 6.5"L, 7.0 x 12.0 mmMounting Hole, PA66HS, Black, 500/pkg

Article Number

157-00053

Type

T50SOSFT7X12U

Color

Black (BK)

Quantity Per

pack

Product Description

One-piece cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Short Description

1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 6.5"L, 7.0 x 12.0 mmMounting Hole, PA66HS, Black, 500/pkg

Global Part Name	T50SOSFT7X12U-PA66HS-BK
------------------	-------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.5
---------------------	-----

Length L (Metric)	165.0
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Outside Serrated
---------	------------------

Width W (Imperial)	0.2
--------------------	-----

Width W (Metric)	5.08
------------------	------

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.06
Thickness T (Metric)	1.52
Height H (Imperial)	0.44
Height H (Metric)	11.3
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.16
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	4.0
Mounting Hole Diameter D (Imperial)	0.28 x 0.47 "
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.28
Mounting Hole Diameter D Max (Imperial)	0.47
Mounting Hole Diameter D Max (Metric)	12.0
Disc Diameter (Metric)	15.2 x 20.2
Disc Diameter (Imperial)	0.60 x 0.80

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com