

Specification Sheet

Part Number: 157-00106



Head allows for a 0.2" lateral adjustment on stud during installation.

Quick and easy installation ideal for manufacturing environment.

1-Piece Cable Tie with Oval Stud Mount, 6.6" Long, 50lb Tensile, Without Thumb Bar, PA66HS, Black, 3000/pkg

Article Number	157-00106
Type	T50SOSSB5-High-E-O-US
Color	Black (BK)
Quantity Per	pack
Product Description	Oval Shaped Stud Mount's special design allows for a 0.2" (5.5 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The mount allows it to be installed onto a weld stud without the use of any tools.
Short Description	1-Piece Cable Tie with Oval Stud Mount, 6.6" Long, 50lb Tensile, Without Thumb Bar, PA66HS, Black, 3000/pkg
Global Part Name	T50SOSSB5-High-E-O-US-PA66HS-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	6.6
Length L (Metric)	167.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Stud Diameter (Metric)	5.0 mm
Stud Diamater (Imperial)	0.20

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)