

Specification Sheet

Part Number: 157-00112



One-piece design allows installers to mount and bundle wire or cables single-handedly.

Fastener delivers high pull-out force for reliable performance, yet it's easy to install.

Can be unscrewed or extracted from threaded holes for easy removal and reusability.

1-Piece Cable Tie with Fir Tree Mount with Disc, 8"L, M6 Threaded Hole, PA66HIRHSUV, Black, 500/bg

Article Number	157-00112
Type	T50ROSFTQM6
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Blind Hole Mount Cable Tie for Threaded Holes offers an easy-to-use method for bundling and affixing cables. The one-piece mount offers a low push-in force and aggressively resists pull out, for secure attachment to panels with thicknesses from 0.02" to 0.28" or threaded blind holes. The disc on top of the mount covers the hole and minimizes ingress of water and debris.
Short Description	1-Piece Cable Tie with Fir Tree Mount with Disc, 8"L, M6 Threaded Hole, PA66HIRHSUV, Black, 500/bg

Global Part Name	T50ROSFTQM6-PA66HIRHSUV-BK
------------------	----------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	222.4
-----------------------------------	-------

Length L (Imperial)	8.0
---------------------	-----

Length L (Metric)	203.2
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.20
--------------------	------

Width W (Metric)	5.08
------------------	------

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Imperial)	0.06
------------------------	------

Thickness T (Metric)	1.5
Height H (Imperial)	0.54
Height H (Metric)	13.83
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.0
Panel Thickness Min (Imperial)	0.13
Panel Thickness Max (Imperial)	0.28
Panel Thickness Min (Metric)	3.25
Panel Thickness Max (Metric)	7.0
Mounting Hole Diameter D (Metric)	M6
Disc Diameter (Metric)	16
Disc Diameter (Imperial)	0.31
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)