

Specification Sheet

Part Number: 157-00131



All-in-one bundling and fastening solution reduces costs and assembly time.

Variety of fir tree diameters and offset lengths address most offset applications.

High-spec materials and superior design deliver excellent performance and value.

1-Piece Cable Tie with Offset Fir Tree with Disc, 12.5 mm Offset, 8.5"L, M6 Hole, PA66HIRHSUV, Black, 500/pkg

Article Number 157-00131

Type T50ROSFTM6SO12.5B

Color Black (BK)

Quantity Per pack

Product Description Offset cable ties route and position bundles away from a mounting hole. Rigid offset bar eliminates potential bending of wire or cables once installed. Multiple offset distances and fir tree sizes cover the majority of industry offset applications. The tie strap's outside serration design provides a smooth surface to protect soft bundles. HellermannTyton's one-piece mounting ties offer a complete solution by both bundling and mounting. Their ideal combination of high-specification materials and superior design suit the needs of complex applications.

Short Description 1-Piece Cable Tie with Offset Fir Tree with Disc, 12.5 mm Offset, 8.5"L, M6 Hole, PA66HIRHSUV, Black, 500/pkg

Global Part Name	T50ROSFTM6SO12.5B-PA66HIRHSUV-BK
------------------	----------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	222.4
-----------------------------------	-------

Length L (Imperial)	8.5
---------------------	-----

Length L (Metric)	215.9
-------------------	-------

Offset Length (Imperial)	0.49
--------------------------	------

Offset Length (Metric)	12.5
------------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.85
Height H (Metric)	21.40
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.65
Mounting Hole Diameter D (Imperial)	0.24 "
Mounting Hole Diameter D (Metric)	M6
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.1
Disc Diameter (Metric)	15.0
Disc Diameter (Imperial)	0.59
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV

UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)