

Specification Sheet

Part Number: 157-00199



An all-in-one bundling and fixing solution reduces costs.

High-specification materials and superior design suit the fixing and bundling needs of complex applications.

1-Piece Cable Tie with Fir Tree Mount, 12.5mm Offset, 0.24 - 0.27 " Mounting Hole, PA66HIRHSUV, Black, 1000/pkg

Article Number	157-00199
Type	T50ROSFT612.5SOVC
Color	Black (BK)
Quantity Per	pack

Product Description	The Offset Cable Ties route and position wire and cable bundles away from a mounting hole. The offset bar between the fir tree and cable tie strap provides a robust and cored-out design to eliminate any potential bending of the wire or cable assembly once installed. The combination of 12.5mm and 25mm offset distances and various fir tree sizes offer coverage for a majority of industry offset routing application. The outside serrations of the tie strap present a smooth surface to the cables preventing any possible damage to soft or delicate bundles. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
Short Description	1-Piece Cable Tie with Fir Tree Mount, 12.5mm Offset, 0.24 - 0.27 " Mounting Hole, PA66HIRHSUV, Black, 1000/pkg
Global Part Name	T50ROSFT612.5SOVC-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.4
Offset Length (Imperial)	0.49
Offset Length (Metric)	12.5
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Width W (Imperial)	0.20

Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.20
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Imperial)	0.66
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)