

Specification Sheet

Part Number: 157-00214



All-in-one bundling and fastening solution reduces costs and assembly time.

Anti-rotational oval fastener forces bundle to travel in intended direction.

Stand-off cable ties route and position bundles above a mounting hole to protect them from rubbing, heat or obstructions.

1-Piece Cable Tie with Fir Tree Mount, 25mm Offset, 9.7"L, 6.1 - 6.9 mm Mounting Hole, PA46, Black, 500/bg

Article Number	157-00214
Type	T50ROSFT625SO
Color	Black (BK)
Quantity Per	pack
Product Description	One-piece stand-off cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. Stand-off feature positions bundles above a mounting hole. The disc prevents rattling in high-vibration applications and protects against debris ingress.
Short Description	1-Piece Cable Tie with Fir Tree Mount, 25mm Offset, 9.7"L, 6.1 - 6.9 mm Mounting Hole, PA46, Black, 500/bg

Global Part Name	T50ROSFT625SO-PA46-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	9.7
---------------------	-----

Length L (Metric)	247.2
-------------------	-------

Offset Length (Imperial)	0.98
--------------------------	------

Offset Length (Metric)	25.0
------------------------	------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Width W (Imperial)	0.20
--------------------	------

Width W (Metric)	5.1
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Thickness T (Metric)	1.5
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.32
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	19.0
Disc Diameter (Imperial)	0.75

Material Polyamide 4.6 (PA46)

Material Shortcut PA46

UV Resistant (Yes/No) No

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)