

Specification Sheet

Part Number: 157-00342



Low-profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

Low Profile M10 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/pkg

Article Number	157-00342
----------------	-----------

Type	T80ROSLPSB10U
------	---------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.
---------------------	--

Short Description	Low Profile M10 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/pkg
-------------------	---

Global Part Name	T80ROSLPSB10U-PA66HIRHSUV-BK
------------------	------------------------------

Minimum Tensile Strength (Imperial)	80
Minimum Tensile Strength (Metric)	355
Length L (Imperial)	8.5
Length L (Metric)	215.9
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.82
Width W (Metric)	20.8
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00342
Height H (Imperial)	0.28

Height H (Metric)	7.0
Mounting Hole Diameter D (Imperial)	0.39 x 0.06 "
Mounting Hole Diameter D (Metric)	M10 x 1.5
Stud Diameter (Metric)	10.0 mm
Stud Diameter (Imperial)	0.39
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)