

Specification Sheet

Part Number: 157-00419



Low-profile head allows mounts to stack, providing more mounting versatility from a single stud

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure

Low Profile M10 Stud Mount Tie, 7.5" L, 80lb Tensile, PA66HIRHSUV, Black, 100/pkg

Article Number 157-00419

Type T80ROSLPSB10U

Color Black (BK)

Quantity Per pack

Product Description One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description Low Profile M10 Stud Mount Tie, 7.5" L, 80lb Tensile, PA66HIRHSUV, Black, 100/pkg

Global Part Name T80ROSLPSB10U-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	80
Minimum Tensile Strength (Metric)	335
Length L (Imperial)	8.5
Length L (Metric)	215.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.82
Width W (Metric)	20.8
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.05
Height H (Metric)	1.35

Stud Diameter (Metric)	10.0 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Privacy Policy](#)

[Cookie Policy](#)

[Terms and Conditions](#)