

Specification Sheet

Part Number: 157-00458



Rotated Offset Fir Tree Cable Ties secures and fastens bundles away from obstructions, heat or sources of abrasion.

All-in-one bundling and fastening solution reduces costs and assembly time.

Variety of fir tree diameters and offset lengths address most offset applications.

Anti-rotational oval fastener forces bundle to travel in intended direction.

1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 8"L, 6.2 x 12.2 mm; 6.5 x 12.5 mm; 6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HIRHSUV, Black, 2500/ctn

Article Number

157-00458

Type

T50ROSFTOVAL15R

Color

Black (BK)

Quantity Per

bag

Product Description

One-piece offset cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. Offset feature positions bundles away from a mounting hole. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.

Short Description	1-Piece Cable Tie with Oval Fir Tree Mount with Disc, 8"L, 6.2 x 12.2 mm; 6.5 x 12.5 mm; 6.5 x 13.0 mm or 7.0 x 12.0 mm Mounting Hole, PA66HIRHSUV, Black, 2500/ctn
Global Part Name	T50ROSFTOVAL15R-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	220
Length L (Imperial)	8.93
Length L (Metric)	227.0
Offset Length (Imperial)	0.59
Offset Length (Metric)	15.0
Fixation Method	Fir Tree for oval holes
Identification Plate Position	none
Releasable Closure	No
Variant	Outside Serrated
Width W (Imperial)	0.92
Width W (Metric)	23.6
Bundle Diameter Min (Imperial)	0.07

Bundle Diameter Min (Metric)	1.8
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.78
Height H (Metric)	19.85
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.26 x 0.49 " 0.24 x 0.48 " 0.28 x 0.47 " 0.26 x 0.51 "
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	17.63 x 23.63
Disc Diameter (Imperial)	0.69 x 0.93

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com