

Specification Sheet

Part Number: 157-00460



Low-Profile head allows mounts to stack, providing more mounting versatility from a single stud.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

1-Piece Low Profile M5/M6 Stud Mount Tie, 8.2" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/ctn

Article Number 157-00460

Type T80ROSLPSB5-6U

Color Black (BK)

Quantity Per pack

Product Description One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution. HellermannTyton's one-piece mounting ties offer the ideal combination of high specification materials and superior design to suit the mounting and bundling needs of complex applications.

Short Description 1-Piece Low Profile M5/M6 Stud Mount Tie, 8.2" Tie, 80lb Tensile Strength, PA66HIRHSUV, Black, 2500/ctn

Global Part Name T80ROSLPSB5-6U-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	80
Minimum Tensile Strength (Metric)	355
Length L (Imperial)	8.2
Length L (Metric)	208.3
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.56
Width W (Metric)	14.22
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00460
Height H (Imperial)	0.25

Height H (Metric)	6.30
Mounting Hole Diameter D (Imperial)	0.2 x 0.03 " 0.24 x 0.04 "
Mounting Hole Diameter D (Metric)	T5 M6 x 1 M5 x 0.8 T6
Mounting Hole Diameter D Min (Imperial)	0.2
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.0
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diameter (Imperial)	0.20 ", 0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2500
Package Quantity (Metric)	2500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)