

Specification Sheet

Part Number: 2NFP0C



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Article Number	161-05036
Type	2NFP
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton’s Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.25" Diameter, PE, Black, 100 ft/roll
Global Part Name	2NFP-PE-BK

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.19
Bundle Diameter Min (Metric)	4.75
Bundle Diameter Max (Imperial)	2
Bundle Diameter Max (Metric)	50.8
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.35
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6.35
Wall Thickness WT (Imperial)	0.045
Wall Thickness WT (Metric)	1.14
Material	Polyethylene (PE)
Material Shortcut	PE

Halogen Free	No
UV Resistant (Yes/No)	Yes
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)