

Specification Sheet

Part Number: 2P9C



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is UL Recognized.

Spiralwrap Protective Sheathing, 0.25" Diameter, PTFE, Natural, 100 ft/roll

Article Number	161-05047
Type	2P
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton’s Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Polytetrafluoroethylene-Teflon (PTFE) offers the widest operating temperature range of any material. It's chemically inert and nonflammable. Natural color is milky white. Available by special order in black and colors.
Short Description	Spiralwrap Protective Sheathing, 0.25" Diameter, PTFE, Natural, 100 ft/roll

Global Part Name	2P-PTFE-NA
Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.19
Bundle Diameter Min (Metric)	4.75
Bundle Diameter Max (Imperial)	2
Bundle Diameter Max (Metric)	50.8
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.35
Nominal Diameter (Imperial)	0.25
Nominal Diameter (Metric)	6.35
Wall Thickness WT (Imperial)	.030
Wall Thickness WT (Metric)	0.76
Material	Polytetrafluoroethylene (PTFE)

Material Shortcut	PTFE
Flammability	UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-449°F to +500°F (-267°C to +260°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com