

Specification Sheet

Part Number: 4NFP0C



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Spiralwrap Protective Sheathing, 0.75" Diameter, PE, Black, 100 ft/roll

Article Number 161-05074

Type 4NFP

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.

Short Description Spiralwrap Protective Sheathing, 0.75" Diameter, PE, Black, 100 ft/roll

Global Part Name 4NFP-PE-BK

Length L (Imperial)	100.0
Length L (Metric)	30.48
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.75
Bundle Diameter Min (Metric)	19.1
Bundle Diameter Max (Imperial)	5
Bundle Diameter Max (Metric)	127.0
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.05
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.065
Wall Thickness WT (Metric)	1.65
Material	Polyethylene (PE)
Material Shortcut	PE

Halogen Free	No
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)