

Specification Sheet

Part Number: 161-05088



- Sheathing allows flexible routing and lead-out of cables
- The inner edges are beveled preventing damage to cables
- Sheathing is reusable and resistant to most chemicals
- Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.88" Diameter, Polyamide, Black, 500ft/roll

Article Number	161-05088
Type	4.5N0H
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.88" Diameter, Polyamide, Black, 500ft/roll
Global Part Name	4.5N0H-PA6-BK

Length L (Imperial)	500.0
Length L (Metric)	152.4
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.5
Bundle Diameter Min (Metric)	12.7
Bundle Diameter Max (Imperial)	5
Bundle Diameter Max (Metric)	127.0
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.05
Nominal Diameter (Imperial)	0.88
Nominal Diameter (Metric)	22.23
Wall Thickness WT (Imperial)	0.032
Wall Thickness WT (Metric)	0.81
Material	Polyamide 6 (PA6)
Material Shortcut	PA6

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	152.40
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)