

Specification Sheet

Part Number: 161-05089



- Sheathing allows flexible routing and lead-out of cables
- The inner edges are beveled preventing damage to cables
- Sheathing is reusable and resistant to most chemicals
- Spiralwrap is U.L. Recognized

Spiralwrap Protective Sheathing, 0.75" Diameter, PA6, Black, 500ft/roll

Article Number	161-05089
Type	4N0H
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize.
Short Description	Spiralwrap Protective Sheathing, 0.75" Diameter, PA6, Black, 500ft/roll
Global Part Name	4N0H-PA6-BK

Length L (Imperial)	500.0
Length L (Metric)	152.4
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.5
Bundle Diameter Min (Metric)	12.7
Bundle Diameter Max (Imperial)	5
Bundle Diameter Max (Metric)	127.0
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.05
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05
Wall Thickness WT (Imperial)	0.032
Wall Thickness WT (Metric)	0.81
Material	Polyamide 6 (PA6)
Material Shortcut	PA6

Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +250°F (-40°C to +121°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	152.40
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com