

## Specification Sheet

Part Number: 161-05090



Sheathing allows flexible routing and lead-out of cables.

The inner edges are beveled preventing damage to cables.

Sheathing is reusable and resistant to most chemicals.

Spiralwrap is U.L. Recognized.

Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Black, 500ft/roll

Article Number 161-05090

Type 2.5NFP0H

Color Black (BK)

Quantity Per pack

**Product Description** HellermannTyton's Spiralwrap protective sheathing provides cable protection and flexible routing. Spiralwrap is wrapped around a group of cables to shield and organize. Polyethylene is ideal for general applications that are not affected by ordinary solvents. Ultraviolet resistant black polyethylene is for outdoor use. It has the same qualities as clear polyethylene, but also contains an ultraviolet absorber which permits it to be used in direct sunlight for long periods of time. Available in colors.

**Short Description** Spiralwrap Protective Sheathing, 0.38" Diameter, PE, Black, 500ft/roll

Global Part Name 2.5NFP0H-PE-BK

Local Order Number 2 161-05090

Length L (Imperial) 500.0

Length L (Metric) 152.4

Variant Spiral Binding

Bundle Diameter Min (Imperial) 0.31

Bundle Diameter Min (Metric) 7.92

Bundle Diameter Max (Imperial) 3

Bundle Diameter Max (Metric) 76.2

Diameter D (Imperial) 0.375

Diameter D (Metric) 9.53

Nominal Diameter (Imperial) 0.38

Nominal Diameter (Metric) 9.53

Wall Thickness WT (Imperial) .052

Wall Thickness WT (Metric) 1.32

Material	Polyethylene (PE)
Material Shortcut	PE
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-76°F to +190°F (-60°C to +88°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1500
Package Quantity (Metric)	457.2
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)