


Specification Sheet

Part Number: 161-64013

Mounting bases can be fastened with screws, cable ties or adhesive.

Can be used to mount any size HWClip.

Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.



Helawrap, Mounting Base with Adhesive, HWBASEA, PA66HIRHS, Black, 50/pkg

Article Number	161-64013
----------------	-----------

Type	HWBASEA
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	With the highly adaptable base plate, cables can be protected alongside most existing structures and installations. The plate can be affixed with screws, with a cable tie threaded through or around the base of the place, or with an adhesive to provide a long-lasting hold.
---------------------	--

Short Description	Helawrap, Mounting Base with Adhesive, HWBASEA, PA66HIRHS, Black, 50/pkg
-------------------	--

Global Part Name	HWBASEA-PA66HIRHS-BK
------------------	----------------------

Length L (Imperial)	1.5
Length L (Metric)	38
Fixation Method	screw-hole
Width W (Imperial)	1.5
Width W (Metric)	38
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Adhesive	Acrylate with base of polyurethane foam
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)