

## Specification Sheet

Part Number: 166-90327

External Metric thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.



Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.

HelaGuard Non-Metallic IP66 Fitting, Straight, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg

Article Number 166-90327

Type HG100-S-M32

Color Black (BK)

Quantity Per pack

Product Description HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard Non-Metallic IP66 Fitting, Straight, M32 Thread, 1.00" Dia, PA66, Black, 10/pkg
Global Part Name	HG100-S-M32-PA66-BK
Length L (Imperial)	2.09
Length L (Metric)	53
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)