

Specification Sheet

Part Number: 166-90824

Integrated Sealing Technology creates a true, one-piece component that reduces installation time and provides error free installation.

Nickel plated brass metric thread provides a secure connection even under dynamic conditions.

Swivel thread feature minimizes cable twisting and provides strain relief.

All-around "teeth" attach firmly to corrugated conduit and deliver a high extraction force.

Fittings deliver IP68 ingress protection against moisture and dirt.



Helaguard Non-Metallic 16mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M16 Thread, NPB, PA66, Black, 10/pkg

Article Number 166-90824

Type HGU16-90M-M16B

Color Black (BK)

Quantity Per pack

Product Description Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.

Short Description	HelaGuard Non-Metallic 16mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M16 Thread, NPB, PA66, Black, 10/pkg
Global Part Name	HGU16-90M-M16B-NPB/PA66-BK
Length L (Imperial)	2.44
Length L (Metric)	62
Variant	90° Elbow
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	16
Material	Polyamide 6.6 (PA66) Nickel Plated Brass (NPB)
Material Shortcut	NPB PA66
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	No

ROHS Compliant

Yes

Package Quantity (Imperial) 10

Package Quantity (Metric) 10

Customs Number 7412200000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)