

Specification Sheet

Part Number: 166-90019



Ensures fast and secure assembly with non-metallic NPT fittings.

HelaGuard® Non-Metallic Locknut, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg

Article Number	166-90019
Type	ALPA0500
Color	Black (BK)
Quantity Per	pack
Product Description	Made of strong and chemical resistant PA66 material, locknut secures non-metallic NPT fittings when used with non-threaded entries.
Short Description	HelaGuard® Non-Metallic Locknut, NPT Thread, 0.50" Dia, PA66, Black, 10/pkg
Global Part Name	ALPA0500-PA66-BK

Variant	Locknut
Thickness T (Imperial)	0.265
Thickness T (Metric)	6.7
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	21
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)