

## Specification Sheet

Part Number: 166-90179

Integrated flip open lid for quick and easy assembly.

Inner rib prevents conduit from slipping.

Easy access mounting hole reduces installation time.

Quick release for easy future access.



HelaGuard® PACC Conduit Clip, 0.50" Dia, PA66, Black, 10/pkg

Article Number 166-90179

Type PACC0500

Color Black (BK)

Quantity Per pack

Product Description Conduit Clips clamp onto corrugated conduits and tubing to secure. Nylon material resists corrosion and chemicals. Conduit clips can also be used on C-shaped DIN rails.

Short Description HelaGuard® PACC Conduit Clip, 0.50" Dia, PA66, Black, 10/pkg

Global Part Name PACC0500-PA66-BK

Length L (Imperial) 1.26

Length L (Metric) 32

Variant Clip

Width W (Imperial) 0.59

Width W (Metric) 15

Height H (Imperial) 1.42

Height H (Metric) 36

Nominal Diameter (Imperial) 0.5

Nominal Diameter (Metric) 21

Mounting Hole Diameter D (Imperial) 0.24 "

Mounting Hole Diameter D (Metric) 6.0 mm

Mounting Hole Diameter D Max (Metric) 6

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)