

Specification Sheet

Part Number: 166-90181

Integrated flip open lid for quick and easy assembly.

Inner rib prevents conduit from slipping.

Easy access mounting hole reduces installation time.

Quick release for easy future access.



HelaGuard® PACC Conduit Clip,1.00" Dia, PA66, Black, 10/pkg

Article Number	166-90181
Type	PACC1000
Color	Black (BK)
Quantity Per	pack
Product Description	Conduit Clips clamp onto corrugated conduits and tubing to secure. Nylon material resists corrosion and chemicals. Conduit clips can also be used on C-shaped DIN rails.
Short Description	HelaGuard® PACC Conduit Clip,1.00" Dia, PA66, Black, 10/pkg
Global Part Name	PACC1000-PA66-BK

Length L (Imperial)	1.89
---------------------	------

Length L (Metric)	48
-------------------	----

Variant	Clip
---------	------

Width W (Imperial)	0.59
--------------------	------

Width W (Metric)	15
------------------	----

Height H (Imperial)	2.01
---------------------	------

Height H (Metric)	51
-------------------	----

Nominal Diameter (Imperial)	1
-----------------------------	---

Nominal Diameter (Metric)	34
---------------------------	----

Mounting Hole Diameter D (Imperial)	0.24 "
-------------------------------------	--------

Mounting Hole Diameter D (Metric)	6.0 mm
-----------------------------------	--------

Mounting Hole Diameter D Max (Metric)	6
---------------------------------------	---

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
-------------------	------

Flammability	UL 94 V-2
--------------	-----------

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com