

## Specification Sheet

Part Number: 166-90308

External NPT thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

IP66 fitting has one-piece construction.



HelaGuard® Non-Metallic IP66 Fitting, Straight, 2" NPT Thread, 2" Dia., PA66, Black, 1/pkg

Article Number 166-90308

Type HG200-S-2000

Color Black (BK)

Quantity Per pack

Product Description HelaGuard Non-Metallic Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description	HelaGuard® Non-Metallic IP66 Fitting, Straight, 2" NPT Thread, 2" Dia., PA66, Black, 1/pkg
Global Part Name	HG200-S-2000-PA66-BK
Length L (Imperial)	2.91
Length L (Metric)	74
Variant	Straight
Outside Diameter OD (Imperial)	3.54
Outside Diameter OD (Metric)	90
Nominal Diameter (Imperial)	2.63
Nominal Diameter (Metric)	67
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)