

Specification Sheet

Part Number: 166-90358

Nickel plated brass thread ensures secure connection with brass plated or nylon fittings.



NPT thread pattern works with metallic or non-metallic threaded fittings.

Use NPT metallic locknuts with 1.25", 1.5" and 2" nylon fittings.

HelaGuard® Metallic Locknuts, 1.25" NPT Thread, 1.25" Dia, PA66, NPB Metal, 4/pkg

Article Number	166-90358
----------------	-----------

Type	ALNPB-1250
------	------------

Color	Metal (ML)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Locknuts work with metric threaded fittings or knockout entries.
---------------------	--

Short Description	HelaGuard® Metallic Locknuts, 1.25" NPT Thread, 1.25" Dia, PA66, NPB Metal, 4/pkg
-------------------	---

Global Part Name	ALNPB-1250-NPB-ML
------------------	-------------------

Material	Nickel Plated Brass (NPB)
Material Shortcut	NPB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	4
Package Quantity (Metric)	4
Customs Number	7415338550

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com