

Specification Sheet

Part Number: 166-90466

External NPT thread provides a secure connection.

Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits.

Elbow features a smooth, swept bore to ease cable installation.

All-around "teeth" attach firmly to conduit and deliver a high extraction force.

Durable nylon material has high resistance to salts, oils, weak acids and solvents.

Product Image

IP66 fitting has one-piece construction.

HelaGuard® Non-Metallic IP66 Fitting, 90-Elbow, 2" NPT Thread, 2" Dia, PA66, Black, 2/pkg

Article Number 166-90466

Type HG200-90-2000

Color Black (BK)

Quantity Per pack

Product Description HelaGuard Non-Metallic 90-Degree Elbow fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. IP66 ingress protection rated fittings.

Short Description HelaGuard® Non-Metallic IP66 Fitting, 90-Elbow, 2" NPT Thread, 2" Dia, PA66, Black, 2/pkg

Global Part Name HG200-90-2000-PA66-BK

Variant 90° Elbow

Outside Diameter OD (Imperial) 3.54

Outside Diameter OD (Metric) 90

Nominal Diameter (Imperial) 2.63

Nominal Diameter (Metric) 67

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -58°F to +275°F (-50°C to +135°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 2

Package Quantity (Metric) 2

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)