

Specification Sheet

Part Number: 166-90826

Integrated Sealing Technology creates a true, one-piece component that reduces installation time and provides error free installation.

Nickel plated brass metric thread provides a secure connection even under dynamic conditions.

Swivel thread feature minimizes cable twisting and provides strain relief.

All-around "teeth" attach firmly to corrugated conduit and deliver a high extraction force.

Product Image

Fittings deliver IP68 ingress protection against moisture and dirt.

HelaGuard® Non-Metallic 21mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M20 Thread, NPB, PA66, Black, 10/pkg

Article Number

166-90826

Type

HGU21-90M-M20B

Color

Black (BK)

Quantity Per

pack

Product Description

Straight snap-on style fittings with nickel plated brass metric threaded fitting provides a true, one-piece component solution; seals are integrated into the fitting body. Durable nylon materials deliver high chemical resistance against salts, oils, weak acids and solvents. Designed for fast assembly and easy removal using a small screwdriver.

Short Description

HelaGuard® Non-Metallic 21mm IP68 Ultra Fitting, 90-Elbow Brass Swivel, Ext M20 Thread, NPB, PA66, Black, 10/pkg

Global Part Name	HGU21-90M-M20B-NPB/PA66-BK
Length L (Imperial)	2.60
Length L (Metric)	66
Variant	90° Elbow
Nominal Diameter (Imperial)	0.5
Nominal Diameter (Metric)	21
Material	Nickel Plated Brass (NPB) Polyamide 6.6 (PA66)
Material Shortcut	PA66 NPB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-58°F to +275°F (-50°C to +135°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial) 10

Package Quantity (Metric) 10

Customs Number 7412200000

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)