

## Specification Sheet

Part Number: 169-60105

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.

Excellent flame resistant properties with higher operating temperature range than PE tubings.



Article Number 169-60105

Type CTPPFR380

Color Black with Blue Stripe (BKSTBL)

Quantity Per carton

**Product Description**

HellermannTyton's Convoluted Tubing, also known at Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offer's excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The Polypropylene flame retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material.

**Short Description**

Convoluted Tubing, Flame Retardant, Slit, 0.38" Dia, PPFR, Black, 1800 ft/ctn

**Global Part Name**

CTPPFR380-PPFR-BK

Length L (Imperial) 1800.0

Length L (Metric) 548.6

Variant Slit

Inner Diameter D (Imperial) 0.380

Inner Diameter D (Metric) 9.65

Diameter D (Imperial) 0.526

Diameter D (Metric) 13.36

Outside Diameter OD (Imperial) 0.526

Outside Diameter OD (Metric) 13.36

Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	9.65
Wall Thickness WT (Imperial)	0.005
Wall Thickness WT (Metric)	0.127
Material	Polypropylene, flame retardant (PPFR)
Material Shortcut	PPFR
Flammability	Self-extinguishing in 60 seconds
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1800
Package Quantity (Metric)	548.64
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)