

## Specification Sheet

Part Number: 170-03067



HellermannTyton braided sleeving installation tools are designed to accommodate a wide variety of braided sleeving products.

Tools are designed and built durable to withstand production environments.

Tools are available in both benchmount and handheld for all kinds of use.

Braided Sleeving, Installation Tool, 1/4" Split Wrap, 1/pkg

|                |           |
|----------------|-----------|
| Article Number | 170-03067 |
|----------------|-----------|

|      |           |
|------|-----------|
| Type | BSWTOOL14 |
|------|-----------|

|       |             |
|-------|-------------|
| Color | Orange (OG) |
|-------|-------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                              |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton offers a wide variety of application tools to assist in the installation of braided sleeving. These application tools are available in both bench mount and handheld styles. |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                             |
|-------------------|-------------------------------------------------------------|
| Short Description | Braided Sleeving, Installation Tool, 1/4" Split Wrap, 1/pkg |
|-------------------|-------------------------------------------------------------|

|                  |                 |
|------------------|-----------------|
| Global Part Name | BSWTOOL14-PL-OG |
|------------------|-----------------|

|                                |                     |
|--------------------------------|---------------------|
| Bundle Diameter Max (Imperial) | 0.25                |
| Bundle Diameter Max (Metric)   | 6.4                 |
| Diameter D (Imperial)          | 0.24                |
| Diameter D (Metric)            | 6                   |
| Nominal Diameter (Imperial)    | 0.25                |
| Nominal Diameter (Metric)      | 6.4                 |
|                                |                     |
| Material                       | Plastic (PL)        |
| Material Shortcut              | PL                  |
| Halogen Free                   | Yes                 |
| UV Resistant (Yes/No)          | No                  |
| Use Conditions                 | For Indoor Use Only |
| Reach Compliant (Article 33)   | Yes                 |
| ROHS Compliant                 | Yes                 |
|                                |                     |
| Package Quantity (Imperial)    | 1                   |
| Package Quantity (Metric)      | 1                   |

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)