

Specification Sheet

Part Number: 170-03124



Center-slit overlapping design allows quick and easy access to the wires and cables for future maintenance or inspection without disassembly.

Flexible material allows it to easily wrap around a variety of component shapes and sizes, making it easier to use than slit-loom tubing or spiral-wrap materials.

A unique weave pattern provides increased coverage and greater resistance to abrasion, dust and debris.

Overlapping design enhances flexibility, allowing it to shift and bend without exposing wire and cables.

Braided Sleeving, Split Wrap, 0.125" Dia, PET, Black, 400 ft/bulk reel

|                     |                                                                                                                                                                                                                                                                                                                                          |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 170-03124                                                                                                                                                                                                                                                                                                                                |
| Type                | BSPSW180B                                                                                                                                                                                                                                                                                                                                |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                               |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                     |
| Product Description | A lateral split semi-rigid braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires. |

|                                |                                                                        |
|--------------------------------|------------------------------------------------------------------------|
| Short Description              | Braided Sleeving, Split Wrap, 0.125" Dia, PET, Black, 400 ft/bulk reel |
| Global Part Name               | BSPSW180B-PET-BK                                                       |
| Length L (Imperial)            | 400.0                                                                  |
| Length L (Metric)              | 121.9                                                                  |
| Bundle Diameter Min (Imperial) | 0.1                                                                    |
| Bundle Diameter Min (Metric)   | 2.54                                                                   |
| Bundle Diameter Max (Imperial) | 0.13                                                                   |
| Bundle Diameter Max (Metric)   | 3.2                                                                    |
| Diameter D (Imperial)          | 0.13                                                                   |
| Diameter D (Metric)            | 3.0                                                                    |
| Nominal Diameter (Imperial)    | 0.125                                                                  |
| Nominal Diameter (Metric)      | 3.18                                                                   |
| Wall Thickness WT (Imperial)   | 0.024                                                                  |
| Wall Thickness WT (Metric)     | 0.61                                                                   |
| Material                       | Polyester (PET)                                                        |

|                              |                                   |
|------------------------------|-----------------------------------|
| Material Shortcut            | PET                               |
| Flammability                 | UL 94 V-0                         |
| Halogen Free                 | Yes                               |
| UV Resistant (Yes/No)        | Yes                               |
| Use Conditions               | For Indoor and Outdoor Use        |
| Operating Temperature        | -94°F to +257°F (-70°C to +125°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| UL Recognized (US)           | Yes                               |
| Package Quantity (Imperial)  | 400                               |
| Package Quantity (Metric)    | 121.92                            |
| Customs Number               | 5808100000                        |

7930 N. Faulkner Road, Milwaukee, WI 53224  
 Phone: (800) 537-1512 | Email: corp@htamericas.com